

www.zinga.eu

30/10/15 - v1

# ZINGACERAM HS

Zingaceram HS is a high solid 2 pack intermediate coat to be applied as a sealer over ZINGA. Due to its high solid (HS) content it shows good compatibility on ZINGA. Zingaceram HS has very good abrasion resistance and excellent corrosion protection properties.

# **PHYSICAL DATA AND TECHNICAL INFORMATION**

# WET PRODUCT

Components	Epoxy resins pigmented with micaceous iron oxide and ceramic fillers, cross linked with a phenalkamine hardener.
Density	- Paint: 1,76 kg/dm³ - Hardener: 1,00 kg/dm³ - Paint + Hardener: 1,64 kg/dm³
Solid content	- 88% by weight (±2%) - 78% by volume (±2%)
Type of thinner	HS Thinner
Flash Point	32°C
Potlife	2,5 - 3 hours
VOC	196 g/L (= 120 g/kg)

# **DRY FILM**

Colour	Grey
Special characteristics	<ul> <li>High solid Content</li> <li>High chemical resistance</li> <li>Temperature resistance of dry film: 95-100°C with peak up to 120°C</li> <li>pH resistance: 2,5 pH to 13 pH</li> </ul>

## PACKING

5 L	4 L part A and 1 L part B
20 L	16 L part A and 4 L part B

## CONSERVATION

Shelf life	1 year in the original and closed container.
Storage	Store in a dry place at temperatures between 5°C and 25°C



30/10/15 - v1

# CONDITIONS

## SURFACE PREPARATION

When the waiting time between the successive coats is abnormally prolonged or in extremely polluted areas, the Zinganised surface can become contaminated. All contaminations that hamper the adhesion of the paint should be removed by appropriate means. Salt deposits or other water-soluble contaminations should be removed with water and brush, water under high pressure or steam. Possible white rust on ZINGA should be removed with water and rigid nylon brush.

# **ENVIRONMENTAL CONDITIONS DURING APPLICATION**

Ambient temperature	- Minimum 5°C
Relative humidity	- Maximum 85% - Do not apply on a damp or wet surface
Surface temperature	<ul> <li>Minimum 3°C above the dew point.</li> <li>No visual presence of water of ice</li> <li>Maximum 60°C</li> </ul>

# **APPLICATION INSTRUCTIONS**

#### GENERAL

Application methods	Zingaceram HS can be applied on top of ZINGA by brush and roller or conventional spray-gun or by airless spraying.
Stripe coat	it is always recommended to treat corners, sharp edges, bolts and nuts before applying a uniform coat.

#### **APPLICATION BY BRUSH AND ROLLER**

Dilution	For optimal use, dilute Zingaceram up to 5% (v%) with HS Thinner.
Type of brush or roller	Industrial round brush Short hair roller (mohair)

## **APPLICATION BY CONVENTIONAL SPRAY-GUN**

Dilution	10-15% (v%) with HS Thinner depending on nozzle size. More dilution for same nozzle size will give a smoother surface finish; which will increase the abrasion resistance of the Zingaceram HS layer.
Pressure at the nozzle	2 to 3 bar for a structured aspect; higher pressure for a smoother aspect.
Nozzle opening	3 mm for a structured aspect; smaller (2,2 to 2,5 mm) for a smoother aspect.

#### **APPLICATION BY AIRLESS SPRAY**

Dilution	0-5% (v%) with HS Thinner depending on nozzle size. More dilution for same nozzle size will give a smoother surface finish.
Pressure at the nozzle	150-250 bar
Pump ratio	45/1
Nozzle opening	0.021 - 0.025 inch / 0,38 - 0,63 mm



www.zinga.eu

30/10/15 - v1

# **APPLICATION ON ZINGA**

Mist (tie) coat	- Application at least 6 hours after ZINGA is touch dry. - 25-30 μm DFT - Diluted according TDS
Full coat	- 2 hours after touch dry of mist coat - DFT = specified DFT - 25-30 μm DFT - Diluted according TDS

# **OTHER INFORMATION**

#### **COVERAGE AND CONSUMPTION**

Theoretical coverage	- For 60 μm DFT: 13 m²/L - For 120 μm DFT: 6,5 m²/L
Theoretical consumption	- For 60 μm DFT: 0,077 L/m² - For 120 μm DFT: 0,15 L/m²
Practical coverage and consumption	Depends upon the roughness profile of the substrate and the application method.

## **DRYING PROCESS AND OVERCOATING**

Drying time	For 60 µm DFT at 20°C in a well-ventilated environment: » Dust proof: 3 hours » Dry to handle: 6 hours » Fully cured: 18 hours » Fully resistant: 7 days
Overcoating with a topcoat	<ul> <li>Overcoatable after minimum 8 hours after touch dry.</li> <li>Maximum overcoat time depends on environmental conditions. Maximum 3 days.</li> </ul>



www.zinga.eu

30/10/15 - v1

#### **RECOMMENDED SYSTEM**

ZINGA 1 x 60-80 μm DFT + Zingaceram HS 1 x 120 μm DFT + Zingaceram EP 1 x 60 μm DFT ZINGA 1 x 60-80 μm DFT + Zingaceram HS 1 x 120 μm DFT + Zingaceram PU 1 x 60 μm DFT	aggri (C5 cond expe ZINC Zing: Zing: Zing: Zing: Zing: Zing: Zing:	aceram HS 1 x 120 μm DFT + aceram EP 1 x 60 μm DFT GA 1 x 60-80 μm DFT + aceram HS 1 x 120 μm DFT +
--	---	--

For more specific and detailed recommendations concerning the application of Zingaceram HS, please contact the Zingametall representative. For detailed information about the health and safety hazards and precautions for use, refer to the Zingaceram HS safety data sheet.

The information on this sheet is merely indicative and is given to the best of our knowledge based on practical experience and testing. The conditions or methods of handling, storage, use or disposal of the product cannot be controlled by us and are therefore outside our responsibility. For these and other reasons we retain no liability in case of loss, damage or costs that are caused by or that are linked in any way to the handling, storage, use or disposal of the product. Any claim concerning deficiencies must be made within 15 days upon reception of the goods quoting the relevant batch number. We retain the right to change the formula if properties of the raw material are changed. This data sheet replaces all former specimens.